For Use with Nu-Calgon's Evap Foam No Rinse°, Evap-Fresh No Rinse°, Blackhawk°, and PenetrateHD° in Tough to Reach Locations

27 IN. FLEXIBLE AEROSOL WAND



DIRECTIONS FOR USE:

This product must be used in accordance to the following directions by HVACR professionals only.

For Nu-Calgon's Evap Foam No Rinse, Evap-Fresh No Rinse Blackhawk, and PenetrateHD aerosols only.

- 1. Wear protective eyewear and gloves.
- 2. Remove aerosol tip from canister. Shake can well.
- **3. IMPORTANT:** In safe location, point Talon tip towards ground and assemble onto canister. A momentary discharge will occur.
- 4. Always remove Talon from aerosol canister when job is complete. Never transport while Talon is assembled to canister.

TALON IS GREAT FOR:



0-9227



2611 Schuetz Rd. | St. Louis, MO 63043 | 800-554-5499 | www.nucalgon.com

(119) Calgon is a licensed trade name.